

Semi-automatic hanger collection mounting machine

«MB»



- Professional, semi-automatic mounting machine for the production of hanger collections
- Precise alignment of samples thanks to electronic length feeding system
- Programmable electronic command
- All samples are fixed from both sides by means of self-adhesive and heat-seal glue paper strips
- Highest productivity with almost no change-over time
- Working width of 80 cm allowing multiple production
- Standard equipment for 5 collections
- Suitable for all materials incl. textiles, home textiles, wallpaper, paper, leather, artificial leather etc.
- Simple operation


Technical Data

Sample size	width	up to 800 mm (31½")
	length	up to 200 mm (8")
Distance between samples	1–200 mm	
Productivity	up to 1000 sample strips/h	
Sample Feed	manually	
Number of sample rows	up to 8 (100 mm)	
Temperature range heat-seal glue	20–200° C	
Electrics	1 x 230 V / 50 Hz	
Weight	430 kg (946 lb.)	

Subject to design changes

Perfect fixing

The samples are glued onto self-adhesive tapes, coated with a special fabric glue. To avoid the samples coming off or shifting during handling, before they get stapled into the relevant hanger caps, the samples are additionally fixed from the top with a heat-seal glue cover tape. Independent heating elements with adjustable temperature activate the heat-seal glue.



...and also for the lower self-adhesive tapes.




Precise alignment of samples at exact, consistent distances from each other is ensured by the highly accurate and reliable advancement of the feeding belt together with the simple manual mounting of the samples. Hanger collections with up to 40 or even more colour samples can now be produced easily with this new development.

Easy set-up

The user is guided through a dialogue-type program, which assists him in creating a new collection in a few easy steps in next to no time. The programmable memory allows you to save up to 100 different collections for a quick recall at a later stage.




The result



Loading of supporting material

Changing and re-filling of the roll holders is very fast and easy for the upper heat-seal glue paper tapes...



The full width collections are cut to size on a POLYTEX sample cutting and pinking machine. The single hanger collections, perfectly glued and fixed, are then placed into a hanger cap which has been pre-printed on one of our card and cap printers type DT3 . This hanger cap is finally stapled by means of a POLYTEX multiple stapler type SE or SR.